

Honeywell Sensing and Control

Search

2TP1-3 (Home : Products : Switches » MICRO SWITCH™ Rocker Switches » Power-duty Rocker Switches » TP)

narrow your search

- Products**
- Controls Monitoring and Lighting (352)
 - Machine Safety (1701)
 - Sensors (6224)
 - Switches (9749)
 - Wireless (39)

- Technology**
- Control and Instrumentation (1052)
 - Electromechanical (9301)
 - Magnetic (541)
 - Optical/Infrared (1042)
 - Thick Film (1764)
 - More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site WGLA and WPMM XYR6000™


find out more

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

Click here to contact us



Actual product appearance may vary.

TP Series Rocker Switch, 2 pole, 2 position, Screw terminal, Flush Panel Mounting

Sales & Service

Distributor Inventory

Overview Specs Documentation Application Notes

Product Specifications

Product Type	MICRO SWITCH™ Rocker
Contact Type	Silver Cadmium Oxide Contacts
Circuitry	DPTD
Action	2 position
Circuitry/Operating action	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Keyway Position</p> </div> <div style="text-align: center;"> <p>Opposite Keyway Position</p> </div> </div>
Mounting	Flush Panel
Lamp Type	Translucent
Termination	Screw
Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc, 0.75 A at 115 Vdc, 0.5 A to 10 A at 0.5 Vac to 277 Vac, 0.5 A to 15 A at 0.5 Vdc to 28 Vdc
LED/Lamp/Neon Voltage	L191: 15 A-125, 250, 277 Vac; 1/2 Hp-125 Vac; 1 Hp-250, 277 Vac; 5 A-120 Vac "L"
Comment	Silver cadmium oxide contacts
Availability	Global
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Series Name	TP

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH Anniversary site