

SMBAMS30P		SMBAMS30PL52		SMBAMS30PL52R		SMBAMS30RA	
<p>All measurements in mm</p>		<p>All measurements in mm</p>		<p>All measurements in mm</p>		<p>All measurements in mm</p>	
<p>Hole center spacing: A = 26, A to B = 13 Hole size: A = 26.8 x 7, B = ø 6.5, C = ø 31</p>		<p>Hole center spacing: A = 26, A to B = 13 Hole size: A = 26.8 x 7, B = ø 6.5, C = ø 31</p>		<p>Hole center spacing: A = 26, A to B = 13 Hole size: A = 26.8 x 7, B = ø 6.5, C = ø 31</p>		<p>Hole center spacing: A = 26, A to B = 13 Hole size: A = 26.8 x 7, B = ø 6.5, C = ø 31</p>	
<ul style="list-style-type: none"> • Flat SMBAMS series bracket with 30 mm hole for mounting sensors • Articulation slots for 90+° rotation • 12-ga. (2.6 mm) cold-rolled steel 		<ul style="list-style-type: none"> • Flat SMBAMS series bracket with space for 70 x 40 mm label • 30 mm hole for mounting sensors • Articulation slots for 90+° rotation • 12-ga. (2.6 mm) cold-rolled steel 		<ul style="list-style-type: none"> • Flat SMBAMS series bracket with space for 60 x 58 mm label • 30 mm hole for mounting sensors • Articulation slots for 90+° rotation • 12-ga. (2.6 mm) cold-rolled steel 		<ul style="list-style-type: none"> • Right-angle SMBAMS series bracket with 30 mm hole for mounting sensors • Articulation slots for 90+° rotation • 12-ga. (2.6 mm) cold-rolled steel 	
Barrel Mount		Barrel Mount		Barrel Mount		Barrel Mount	
<p>Used with</p>		<p>Used with</p>		<p>Used with</p>		<p>Used with</p>	
QS30 S30 SM30/SMI30 T30	T30U EZ-LIGHT T30 PICO-GUARD Point	EZ-LIGHT T30		EZ-LIGHT T30		QS30 S30 SM30/SMI30 T30	T30U EZ-LIGHT T30 PICO-GUARD Point
Base Mount		Base Mount		Base Mount		Base Mount	
<p>Used with</p>		<p>Used with</p>		<p>Used with</p>		<p>Used with</p>	
Q40 Q45 OMNI-BEAM OTB/LTB VTB STB QT50R	QT50U Q45U Q45UR K50 EZ-LIGHT K50L EZ-LIGHT TL50 EZ-LIGHT CL50 WL50 Work Lights	VTB K50 EZ-LIGHT K50L EZ-LIGHT CL50		VTB K50 EZ-LIGHT K50L EZ-LIGHT CL50		Q40 Q45 OMNI-BEAM OTB/LTB VTB STB Q45U	Q45UR QT50U QT50R K50 EZ-LIGHT K50L EZ-LIGHT TL50 EZ-LIGHT CL50 WL50 Work Lights

More on next page